



## FUZZYSCAN L780BT

### 1D Cordless Imager



### Designed for the tough demands of enterprise barcode scanning

Rugged, powerful and swift, the L780BT delivers high-performance along with Bluetooth mobility. Its robust housing protects against inadvertent drops, while the sharp laser beam expedites barcode targeting. The L780BT is here to help you get the job done, whether it is scanning products on a counter or checking inventory status around the warehouse.

- Integrated with the latest Bluetooth wireless technology
- Smart cradle offers radio coverage of over 100 meters
- Works with most Android, iOS and Windows mobile devices
- Batch Scanning for simple stocktaking
- Sharp laser beam for quick and precise aiming
- Supports PDF417 and Composite Codes
- Reads various challenging and problematic barcodes
- Clear audio and visual feedback
- Optional vibrator for quiet or noisy environments
- Configuration can be done through iCode
- Advanced data formatting with DataWizard Premium
- System security development using DataWizard Premium

### Wireless Convenience

#### Movement and Compatibility

Embedded with Bluetooth technology, the L780BT provides cordless mobility and the freedom of movement required by many applications. It can also be easily paired with the majority of popular Bluetooth devices, including Windows, iOS and Android phones. Connection can be made under HID or SPP mode.

#### The Cradle Advantage

The L780BT can be paired with Cino's smart cradle, which is Bluetooth-enabled with a coverage distance of over 100 meters. The latter can serve as an instant plug-and-play cordless solution if your host device lacks Bluetooth capabilities.

Under PICO mode, the smart cradle can support up to 7 scanners at once. This allows you to centralize the data transmission process, gathering multiple connections on a single cradle.

### Practical Features

#### "On-the-Spot" Data Transmissions

Under "Online Scanning", L780BT sends barcode data to its host device immediately after each scan.

If "Out-of-range scanning" is also enabled, this imager will store up to 5,000 scans of EAN barcodes when it loses radio connection with the host device. Upon reconnection, the imager will automatically send out all stored data.



**Manufacturing**



**Warehousing**



**Distribution Center**



**Retail**

### Efficient Stocktaking

“Batch Scanning” can be selected for inventory work. Barcode data is kept in the imager and will only be sent, as a batch, to the host device when you activate transmission.

80,000 scans of EAN barcodes can be stored in the imager under this mode. Quantity value and time-stamp may be added to data immediately following capture.

### Data Verification Made Easy

“Validation Scanning” enables the imager to record master data. The latter is then compared to information that is subsequently read. Should they not be a match, the imager will issue warning beeps. This mode facilitates validation tasks in warehouses and factories, such as verifying the uniformity of items in a lot.

### Power that Lasts

L780BT incorporates an advanced power management system that maximizes the number of scans per charge. Depending on usage, a full charge may be sufficient for a whole day’s work. Battery status indications are available to help you focus on the tasks at hand, and not on the next recharge.

### Scan All Your Needs

#### Tackle Stacked Symbolologies

L780BT is designed to scan a vast array of 1D and stacked symbolologies, whether displayed on paper, plastic or electronically. Stacked-linear barcodes that can be read by the scanner include PDF417, GS1 Databar Stacked, and composite codes.

#### Ready for Challenges

Empowered by the FuzzyScan imaging platform, this scanner is primed to read various challenging and problematic barcodes. For example, poor quality, distorted, dirty, damaged, and overwrapped barcodes, as well as electronic barcodes on dimly-lit displays.

#### One Tool for Different Jobs

L780BT delivers superior readings on high-density barcodes, in addition to exceptional scan range on regular barcodes. Its high performance and capabilities make it a versatile scanner that is well-suited for diverse applications.

### Enhanced User Experience

#### Sharp Aimer for Rapid Targeting

The scanner’s sharp laser beam helps users aim faster and with greater accuracy. L780BT also projects a bright red illumination that allows for rapid barcode captures, even under low ambient lighting. Unlike traditional laser scanners, L780BT makes use of advanced imaging technology to capture barcodes.

#### Clear Audio and Visual Feedbacks

This barcode scanner contains a programmable beeper with adjustable sound volume. Its LED lights provide conspicuous, multi-color indications. Along with the optional vibrator, these sensory feedbacks work in concert to promote a greater scanning experience.



## Unique DataWizard Premium

### Optional Vibrator for Quiet or Noisy Environments

An optional vibrator is available, offering tactile confirmation of good reads. It is ideal for places where the scanner's beeps might be disruptive, such as a library or in hospital rooms where patients are resting. Vibrations may also be preferable in environments where beeping sounds may be drowned out by loud noises, e.g. manufacturing plant.

### Built for Lasting Performance

When we designed the L780BT, durability and ergonomics were at the top of our priority list. With an over-mold construction, this imager can withstand 2.0-meter drops to concrete. Its handle allows for a natural grip, offering superior comfort throughout the day. Moreover, the imager's elegant outline is sure to complement the decors of professional establishments.

## Value Beyond Measure

### Simplified Configuration Process

The iCode is a configuration barcode. It can be embedded with more than one command, thereby enabling the simultaneous change of numerous parameters. Instead of configuring their Cino imagers with multiple barcodes, users can achieve the same results with a single iCode.

Simply choose your desired settings in the FuzzyScan PowerTool, and click on the "iCode" button to generate a comprehensive barcode that embodies them all.

### Customized Functionalities

DataWizard Premium lets you write data or security scripts which can then be used to program Cino scanners for customized tasks. The script language is similar to BASIC and easy to learn for experienced programmers.

This exclusive feature is included in the FuzzyScan PowerTool and offered to Cino clients without extra charge.

### Advanced Data Formatting

Through data scripts, your scanners can be programmed for intricate formatting duties that would otherwise be assigned to the host device. For example: parsing raw data from driver licenses, adding preambles or postambles, and more.

### System Security

Set your host system to prompt scanners for a validation key before allowing connection. Develop a security script containing the validation key and install this script on approved scanners. This will prevent random scanners from accessing the host system.

# SPECIFICATIONS

## Performance Characteristics

Optical System	High performance linear imaging engine
Print Contrast	20% minimum reflective difference
Light Source	630nm visible red LED with laser aiming
Minimum Resolution	3 mil (Code 39, PCS 0.9)
Reading Range *1	13 mil (0.33mm) UPC/EAN up to 24" 20 mil (0.5mm) Code 39 up to 34"
Scan Rate	Dynamic scanning rate up to 500 scans per second
Reading Direction	Bi-directional (forward and backward)
Pitch / Skew / Tilt	±65° / ± 65° / ± 55°
Operating Modes	Trigger, Presentation
Configuration Setup	Command barcodes iCode FuzzyScan PowerTool
Data Editing	DataWizard Premium
User Interfaces	Blue link indicator and 2-color status indicator Programmable beeper Optional vibrator

## Electrical Characteristics

Battery	3.7V, 2600mAh Li-ion rechargeable battery
Battery Charge Time	Approx. 4 ~ 5 hours per full charge
Scans per full Charge	More than 126,000 scans and transmissions
Operating Voltage	5VDC ± 10%
Operating Current	Charging: Max.680 mA Standby: Max.85 mA (Scanner with Smart Cradle)

## Communication Characteristics

RF Standard	Bluetooth v4.0
RF Frequency Band	2.402 ~ 2.4830 GHz unlicensed ISM band
Radio Link Modes	PAIR, PICO, SPP, HID
Communication Range	More than 100 meters in open space when working with Smart Cradle, line of sight
Supported Profiles	SPP, HID

## Physical Characteristics

Dimensions	97.8 mm (L) x 70.5 mm (W) x 156.2 mm (D) 3.85 in. (L) x 2.77 in. (W) x 6.15 in. (D)
Weight	230g (Battery included)
Color	Light Gray or Black

## Supported Symbolologies

1D Linear Codes	Code 39, Code 39 Full ASCII, Code 32, Code 39 Trioptic Code 128, GS1-128, Codabar, Code 11, Code 93 Standard & Industrial 2 of 5, Interleaved & Matrix 2 of 5 German Postal Code, China Postal Code, IATA UPC/EAN/JAN, UPC/EAN/JAN with Addendum Telepen, MSI/Plessey & UK/Plessey GS1 DataBar (formerly RSS) Linear & Linear Stacked
Linear-stacked	PDF417, Micro PDF417, Codablock F, Composite

## User Environment

Drop Specifications	Withstands multiple drops from 2.0m (6.6ft) to concrete
Environmental Sealing	IP42
Operating Temperature	-10 °C to 50 °C (14 °F to 122 °F)
Storage Temperature	-40 °C to 70 °C (-40 °F to 158 °F)
Humidity	5% to 95% relative humidity, non-condensing
Ambient Light Immunity	0 ~ 100,000 Lux
ESD Protection	Functional after 15KV discharge

## Safety & Regulatory

EMC & Radio	CE, FCC, BSMI, RCM, KC, NCC, VCCI, MIC
Safety *2	LED Eye Safety IEC62471, Exempt Group Laser Eye Safety IEC60825-1, Class 1
Environmental	Compliant with RoHS directive

## Accessories

<b>Smart Cradle</b>	
RF Standard:	Bluetooth v4.0
Battery Charging:	Fast charge
User Interfaces:	1 blue link indicator 2-color status indicator Beeper, Paging / Reset button
Host Interface:	USB HID (USB Keyboard) USB VCOM (USB COM port emulation) Standard RS232
<b>Charging Cradle</b>	
Battery Charging:	Fast charge
User Interface:	1 blue power indicator
<b>Interface Cables</b>	RS232 Serial Cable USB Cable
<b>Others</b>	SD112 Bluetooth Smart Dongle 5VDC Power Supply Unit BT2100 Battery Pack (2600mAh) US100 SmartStand US50 Hand-free Stand Universal Holder

1. The Reading Range are measured under Cino's test environmental condition.
2. Don't stare into the Laser beam.

